



HS-2 LABORATORY HEAT SEALER



The satisfactory development, manufacture, conversion and application of flexible packaging films necessitates using precise methods of research and quality control. The HS-2 was developed to precisely control the parameters essential in determining the heat seal threshold. Especially suited for flexible packaging materials, the HS-2 features accurate control of temperature, pressure and dwell time of a standard surface area sealing jaw. Because of its stability, repeatability and reliability, the test machine quickly became the industry standard.

Temperature control:

Digital P.I.D. auto tuning controller, range 0–400°C with platinum resistance PT100 sensor.
Accuracy +/- 0.5% F.S.
Operation accuracy +/- 0.5% of range.

Pressure control:

Precision regulator controller 0–100 PSI
repeatability 0.02 PSI.
Indication via digital indicator and strain gauge transducer.
Accuracy 0.25% F.S.
Operation accuracy +/- 5% of range.

Dwell time control:

Digital quartz timer, range 0.1–10 secs.
Accuracy +/- 0.01%.
Operation accuracy +/- 5% F.S.

Delay time:

Timing relay adjustable 0–10 secs.

Jaws:

Fitted as standard 25 x 50mm ground flat top jaw and silicone rubber (60 shore) bottom jaw. Optional matching ground flat bottom jaw. Optional matching profiled jaws, top and bottom assembly. 120° x 1.8mm pitch.

Jaw alignment:

Adjustable in four planes top and bottom.

Pressure supply:

Minimum 3 bar (43 PSI).
Maximum 7 bar (100 PSI).
Compressed air clean and dry.

Supply voltage:

240 VAC 50/60 Hz (110 VAC 50/60 Hz on request).



Equipos de control de calidad

Tel.: (+34) 902 450 160


Fax: (+34) 902 433 088

ermec@ermec.net

www.ermec.net



BS EN ISO 9001 Certificate No. 6220

VERTRIEB  SERVICE

Willi-Brückner-Strasse 1 · D-56564 Neuwied
Fon +49.2631.3933-0 · Fax +49.2631.3933-33
e-mail: info@lippke.com · Internet: www.lippke.com

Lippke

PAUL LIPPKE HANDELS-GMBH
Prozess- und Laborsysteme

E&OE